


### PRODUCT DESCRIPTION

- » Extra small mini handpiece for deburring and engraving work
- » Smooth running even at the highest speeds
- » Ergonomic aluminium housing with low weight
- » Integrated motor cooling for the longest possible switch-on and service life
- » Illuminated on/off switch conveniently located directly on the handpiece
- » Important: GESM 1000 must have at least firmware version v009a installed.  
Firmware update instructions are available for download.



### SCOPE OF DELIVERY

- » Collect chucks,  $\varnothing$  3 mm, with slotted spring pin
- » Collet wrench
- » Motor cable

| Weight | d1 | lk <sup>1)</sup> | Performance | n                                | No.              | EUR |
|--------|----|------------------|-------------|----------------------------------|------------------|-----|
| 95 g   | 3  | 1.85 m           | 260 W       | 1,000 - 70,000 min <sup>-1</sup> | GESM 2004/260/70 | <>  |

1) cl: cable length

**i** Spare parts and repair by request

### CHARACTERISTICS

| GESM 2004     | Value              |
|---------------|--------------------|
| Motor type    | Brushless DC motor |
| Torque        | 3 Ncm              |
| Concentricity | < 0.02 mm          |